

MAX
Calma

Max Calma Z
User Guide

Product Range



How To Use Max Calma Z 100 x 140cm Acoustic Pod



Dimmable Light Control



Acoustic Felt Ceiling



Desktop Socket



Ventilation System Control

1

Max Calma Z 100x140 is ideal for individual work for long hours, video conferences and phone calls.

2

The occupancy indicator located on the corners of the pod, shows the availability of Acoustic Pod (Red: Occupied, Green: Free) - Optional

3

When you enter the Calma Small pod the movement sensor will automatically detects you and starts the fan. Once you are inside; you can adjust by holding to dim or increase the intensity of the light. You can save the light intensity by double - clicking for later.

4

The retractable worktable enables flexibility for user- Retractable up to 180mm, with cable tray.

5

The pod is compatible with all-in-one PC or Screen.

6

Your Calma Z has a media port system integrated into the wall. This includes: 1x Universal plug, 1x USB-A, 1x USB-C, 1x Adjustable ventilation controller. (Available with RJ45 upon request) - you can charge your phone and laptop thanks to the socket.

7

The Max Calma Z is available with an in-built media wall. This includes: VESA Mount (Up to 27" All in One PC or Monitor) + Dimmable Face Light Control. You can activate the face light and adjust it to the level you want. When you press the same button twice, you can save the light intensity you have determined.



Points to Consider:



Make sure the ventilation holes on the sides of Calma Z are not blocked from outside.



Do not plug any appliances more than 220 V.



Make sure that the Calma Z is not plugged in before you open the access cover on top.



Before moving Calma Z to relocate, always raise its feet off the ground and move it on wheels. Make sure the Calma Z is positioned back on the feet when the relocation is complete.



Keep the door closed all times.



Do not leave your charger and laptop plugged.



Do not smoke inside.



Keep fire away.